

## DETAILED SPECIFICATION FOR QCM SENSOR PART # QCM6125CrAU115-115-S

### KEY FEATURES

<input checked="" type="checkbox"/> 6 MHz
<input checked="" type="checkbox"/> 12.5 MM SENSOR DIAMETER
<input checked="" type="checkbox"/> 11.5 / 11.5 MM ELECTRODE DIAMETER
<input checked="" type="checkbox"/> CHROMIUM / GOLD ELECTRODES
<input checked="" type="checkbox"/> SLOAN / ULVAC TEST JIG COMPATIBLE
<input checked="" type="checkbox"/> 100% TESTED ELECTRICALLY AND VISUALLY
<input checked="" type="checkbox"/> SPUTTERED ELECTRODES

### DESCRIPTION

For use in film thickness monitors. Very reliable function due to good adhesion of electrodes. Long operational life time. Same large size electrodes on both sides.

### GENERAL

Item	Parameter	Value
1.0	Sensor design	Plano-Convex
2.0	Angle of cut	AT
3.0	Jig compability	Sloan, Ulvac

### ELECTRICAL

4.1	Nominal frequency	6.000 MHz
4.2	Center frequency	5.983 MHz
4.3	Frequency tolerance	+/- 7 KHz
4.4	Q-value	> 150 000
4.5	Shunt capacitance, C0	Typ. 21 pF

### ELECTRODES


5.1	Front electrode diameter	11.5 mm
5.2	Front electrode material	Cr/Au Chromium / Gold
5.3	Back electrode diameter	11.5 mm
5.4	Back electrode material	Cr/Au Chromium / Gold
5.5	One sided contacting	No

### MECHANICAL & DRAWING


6.1	Nominal blank diameter	12.5 mm
6.2	Crystal axes orientation	No
6.3	Surface appearance	Matte
6.4	Bevel	No



Quartz Crystal  
Electrical equivalent 2pole




Front electrode



© 2013-2014 Quartz Pro  
Image protected by Digimarc ®

Back electrode



## DETAILED SPECIFICATION FOR QCM SENSOR PART # QCM6125CrAu115-115-S

### MARKING / LABEL

7.1	QR code	Simple info readout with QR app
7.2	Part Number	QCM6125CrAu115-115-S
7.3	Nom. Frequency	6.000 MHz
7.4	Sensor diameter	12.5 mm
7.5	Electrode material	Cr/Au Chromium / Gold



### PACKAGING & STORAGE

8.1	Sensor package type	Revolving plastic depository with a transparent lid for easy inspection
8.2	Storage quantity	10 covered dust and shock protected storage positions and 1 open position for ejection
8.3	Package protection	Package is protected with a vacuum sealed plastic bag for prolonged storage and shipping
8.4	Storage recommendation	After opening plastic vacuum bag preferably store in dust free dry Air or Nitrogen @ room temperature.
8.5	Cleaning	No cleaning necessary before use. However after prolonged storage in humid air a light cleaning in a ultrasonic bath of either ultraclean water or alcohol without any denaturation can be done to remove adsorbed molecules on the surfaces

### REVISION HISTORY

	Date	Description
9.0	2009.02.06	First issue
9.1	2014.08.15	New detailed datasheet
9.2		
9.3		
9.4		
9.5		

## DETAILED SPECIFICATION FOR QCM SENSOR PART # QCM6125CrAu115-115-S

### PRODUCT PART NUMBER DESIGNATION AND INTERPRETATION. FOR MORE ALTERNATIVES SEE PAGE 3

Item	Product Category	1. Nominal Frequency	2. Sensor Diameter	3a. Coating Multiple layer 3b. Coating Single layer	4. Electrode Diameter Ø Front-Back	5. Jig/Holder Compability
Parameter	QCM	6 MHz	12.5	Chrome/Gold	11.5-11.5mm	Balzer
Code	QCM	6	125	CrAu	115-115	B

Part number designation : QCM6125CrAu115-115-S

### PART NUMBER DESIGNATION OPTIONS (AVAILABLE TYPES)

1. Nom Frequency	Designation	2. Sensor Diameter Ø	Designation	3a. Coating -Multiple layer	Designation
5.00 MHz	5	8.90 mm	089	Chromium/Gold	CrAu
6.00 MHz	6	12.45 mm	125	Silver/Aluminum	AgAl
9.00 MHz	9	14.0 mm	140	Nickel/Silver	NiAg
10.7 MHz	10	25.4 mm	254	Titanium/Gold	TiAu
				Chromium/Gold/SiO2	CrAuSiO2
				Nickel/Silver	NiAg

4. Electrode Diameter	Designation	5. Jig/Holder Compability	Designation	3b. Coating -Single layer	Designation
5.1-5.1 mm	051-051	Balzer	B	Gold	Au
5.4-5.4 mm	054-054	Sloan/Ulvac	S	Silver	Ag
7.5-5.0 mm	075-050	Inficon*	I	Copper	Cu
7.5-7.5 mm	075-075	Q Sense	Q	Titanium	Ti
11.5-11.5 mm	115-115	Maxtek 25.4 mm	M	Aluminum	Al
12.0-5.0 mm	120-050	HC-50	H		
12.8-6.4 mm	128-064	Custom	C		
13.0-6.4 mm	130-064				
13.0-13.0 mm	130-130				
13.3-6.0 mm	133-060				

\* also compatible with Maxtek, Sycon, Sigma ,Intellimetrics, Fil-Tech, Phelps

**Custom made products:** In case you need something else that is not listed above, please feel free to ask and we will check our possibilities. Use our contact form under Contact. [www.quartzpro.com](http://www.quartzpro.com)

